

SG *GreenCoat Incolore* / SD *GreenCoat Incolore Standard*



SG *GreenCoat Incolore* is a clear and transparent gelcoat specially designed for aesthetic parts.

SG *GreenCoat Incolore* has a good UV resistance with 51% of biobased carbon in the resin part and 37% in the final mixture.

		SD Green Coat Incolore Standard
Reactivity level		Standard
Initial viscosity (mPa.s)	@ 20 °C	110000
	@ 30 °C	120000
Pot Life (150 g)	@ 20 °C	14 min
	@ 30 °C	6 min
Mixing ratio	By weight	100 / 48
	By volume	100 / 50
TG1 max onset	°C	71
Open time	@ 20° C	40 min
	@ 30 °C	20 min
Overcoating mini time	@ 20° C	07 h 00
	@ 30 °C	03 h 30
Overcoating maxi time	@ 20° C	24 h 00
	@ 30 °C	13 h 20
Dust-free	@ 20° C	03 h 30
	@ 30 °C	02 h 00
Hard to the touch	@ 20° C	10 h 00
	@ 30 °C	05 h 00
Consumption (g/m ²)	(g/m ²)	1000 - 3000
Hardness	(Shore D 0-15 s)	88 - 86

SG GreenCoat Incolore is a clear and transparent gelcoat specially designed for aesthetic parts.

SG GreenCoat Incolore has a good UV resistance with 51% of biobased carbon in the resin part and 37% in the final mixture.

Generally intended for the production of epoxy laminates in open molds, infusion or RTM. We recommend applying 400 to 500 g/m² of gel coat in the mold and apply the epoxy system as soon as possible.

Fastening is optimized by the use of matt 100 or 200 g/m² in the first layer.



Epoxy resin SG Green Coat Incolore

Appearance		gel
Color		purple
Gardner color		≤ 0
Viscosity (mPa.s)	@ 15 °C	6400 ± 1300
	@ 20 °C	3700 ± 750
	@ 25 °C	2200 ± 450
Density	@ 20 °C	1,1700
Storage (months)	@ Ta	24
Dry extract %		100

Hardener(s)


		SD Green Coat Incolore Standard
Appearance		gel
Color		colourless
Gardner color		≤ 0
Reactivity level		Standard
Viscosity (mPa.s)	@ 15 °C	78450 ± 15700
	@ 20 °C	62400 ± 12500
	@ 25 °C	51450 ± 10300
Density	@ 20 °C	1,0500
Storage (months)	@ Ta	12
Dry extract %		

Mixe(s) SG GreenCoat Incolore / SD GreenCoat Incolore Standard


		SD Green Coat Incolore Standard
Appearance		gel
Color		colourless
Mixing ratio		
	By weight	100 / 48
	By volume	100 / 50
Initial viscosity (mPa.s)	@ 20 °C	110000
PP 50 mm / 10 s ⁻¹	@ 30 °C	120000
Density	@ 20 °C	1,1646
Consumption (g/m ²)	(g/m ²)	1000 - 3000
Spread rate (g/m ²)	(m ² /kg)	0,33 - 1
Thickness (mm)	(mm)	1 - 3

Reactivity for 150 g

	20 °C	30 °C	°C
Exothermic temperature (°C)	131	158	
Exothermic peak time	20 min	13 min	-
Time to reach 50 °C	14 min	6 min	-



@ 20 & 30 °C



Coating properties :

		SG Green Coat Incolore / SD Green Coat Incolore Standard		
Curing cycles	→	24 h @ TA + 8 h @ 60°C		
DSC glass transition				
TG1 onset	°C	69		
TG1 max onset	°C	71		
Hardness				
Shore D 0-15s		88 - 86		

Tests carried out on samples of pure cast resin, without prior degassing, between steel plates.

Measures undertaken according to the following norms:

Mechanical tests:

Tension:	NF EN ISO 527-2:2012
Flexion:	NF EN ISO 178:2011
Compression:	NF EN ISO 604:2004 or NF EN ISO 844:2014 (foam product)
Charpy impact strength:	NF EN ISO 179-1:2010
Shear Strength:	ASTM D732-17 (Punch Tool)
Interlaminar shrinkage strength:	ASTM D5528-13
Toughness (GIC et KIC) :	ISO 13586:2000

Water absorption: Internal. Polymerization according to cycle, machining, weighing, time spent in distilled water at 70 °C / 48 hours, weighing 1 hour after emerging,

Bonding Strength Double lap shear:	ASTM D3528-96
	ADH = adhesive failure
	COH = cohesive failure
	TLC = thin-layer cohesive failure
	FT = fiber-tear failure.
	LFT = light-fiber-tear failure

Thermal tests:

Glass transition DSC:	NF EN ISO 11357-2:2014 -5°C to 180 °C under nitrogen gas
	T_{G1} or Onset: 1 st scan at 20 °C/min
	T_{G1} maximum or Onset: 2nd scan at 20 °C/min

Glass transition DTMA:	Temperature ramp 0 °C to 180 °C @ 2°C/min under normal atmosphere
	NF EN ISO 11357-1:2016 T_g onset G'
	ASTM D4065-12 T_g peak G''

Physical tests:

Gardner color:	NF EN ISO 4630:2016	Visual method
Refractive index:	NF ISO 280:1999	
Viscosity:	NF EN ISO 3219:1994	Rheometer 50 mm, shear 10 s ⁻¹
Density on liquids:	ISO 2811-1:2016	Pycnometer
Density on solid:	NF EN ISO 1183-3:1999	Helium Pycnometer
Density on foam:	NF EN ISO 845:2009	
Gel time:	Cross G' G''	Rheometer CP50 - Shear rate 10 s ⁻¹
Green Carbone content:	ASTM D6866-16 or XP CEN/TS 16640 Avril 2014	

TA:	Ambient temperature (20 to 25 °C)
NC:	No information Communicated
NB:	No Breaking (maximum flexion deformation : 15 %)

Table 1st page:

Pot Life:	Time to reach 50 °C or time limit for use
Gel time:	Intersection of tangents on the viscosity curve of 1 mm thick layer
Release time:	Time required to obtain sufficient mechanical strength to release
Minimum Vacuum Time:	Time in which vacuum can be applied (25000 mPa.s)
Maximum Vacuum time:	Limit time below which a vacuum can be applied (G'G'' crossing)
Optimum Infusion time:	Time to reach 400 mPa.s
Max Infusion Time:	Time to reach 25000 mPa.s
Vacuum cut-off time:	Time to reach G'G'' crossover + 20%

LEGAL NOTES:

Information given in writing or verbally, in the context of our technical assistance and our trials, does not engage our responsibility. Information is given in good faith based on SICOMIN's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with SICOMIN's recommendations. We advise users of SICOMIN products to check by some practical trials that they are suitable for the intended processes and applications. The customer's storage, the use, the implementation and the transformation of the supplied products are not under SICOMIN's control and entirely under the sole responsibility of the user.

SICOMIN reserves the right to change the properties of its products. All technical data stated in this Product Data Sheet are based on laboratory tests. Actual measured data and tolerance may vary due to circumstances beyond our control.

If our responsibility should nevertheless be involved, it would be, for all the damages, limited to the value of the goods supplied by us and processed by the customer. We guaranty the non-reproachable quality of our products, in the general context of sales and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.